



U1

43	P60/C-RTS0	39	P30/CLK3
42	P61/CLK0	38	P31/SIN3
41	P62/RxD0	37	P32/SOUT3
40	P63/TxD0	36	P33
31	P64/C-RTS1/CTS0/CLKS1	35	P34
30	P65/CLK1	34	P35
29	P66/RxD1	33	P36
28	P67/TxD1	32	P37
27	P70/C-RTS1/CTS0/CLKS1	51	P20
26	P71/RxD2/SCL/TA0in/CLK1	50	P21
25	P72/CLK2/TA1out/V/RXD1	49	P22
24	P73/C-RTS2/TA1in/V/TXD1	48	P23
23	P74/TA2out/W	47	P24
22	P75/TA2in/W	46	P25
21	P76/TA3out	45	P26
20	P77/TA3in	44	P27
19	P80/TA4out/U	59	P10/AN20
18	P81/TA4in/U	58	P11/AN21
17	P82/INT0	57	P12/AN22
16	P83/INT1	56	P13/AN23
15	P84/INT2/Zphase	55	P14
14	P85/NMI/SD	54	P15/INT3/ADTrq/IDW
5	P90	53	P16/INT4/IDV
4	P91	52	P17/INT5/INPC17/IDU
3	P92	67	P00
2	P93	66	P01
1	P95	65	P02
80	P96	64	P03
79	P97	63	P04
77	P100	62	P05
76	P101	61	P06
74	Vref	60	P07
73	P101/AN1	8	P86
72	P102/AN2	7	P87
71	P103/AN3	10	Xout
70	P104/AN4/KI0	12	Xin
69	P105/AN5/KI1	9	RESET
68	P106/AN6/KI2	11	Vas
6	CNVss	76	AVss

Renesas Technology America		
Title		
SKP16CMINI-28		
Size	Document Number	Rev
B		1.1
Date:	Thursday, July 28, 2005	Sheet 1 of 1